

tesa[®] Double-Sided Adhesive Pads for Transparent & Glass



Product Information

BNR 77731

Product Description

Double-Sided Adhesive Pads for Transparent & Glass. For the temporary attachment of lightweight paper items and decorations.

Product Features

- For lightweight objects like cards or notes
- For short-term applications
- Removable without a trace
- UV-resistant

Application Fields

How to apply – Step by step

- 1. Start by making sure that the surface is clean and dry. silicone-free window cleaner or methylated spirit work well.
- 2. Apply the transparent pads first onto your object or the surface.
- 3. Then simply press your object onto the surface.
- 4. When you're ready to change things, gently peel the pads from your surface. They won't leave any stains.

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

• Type of adhesive	synthetic rubber & epoxy resin	Total thickness	700 µm
Properties/Performance Values			
Chemical resistanceHumidity resistance	no no	Solvent freeUV resistant	yes yes
Residue free removal	yes	Waterproof	no
Reusable	no		



tesa® Double-Sided Adhesive Pads for Transparent & Glass

Product Information

Disclaimer

tesa[®] products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa[®] product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



Page 2 of 2 – as of 20/01/23 – en-US